

INSTRUCTIONS FOR: TOPCHEST 8 DRAWER 1040MM HEAVY-DUTY/ ROLLCAB 11 DRAWER 1055MM HEAVY-DUTY MODEL No's: PTB104008SS, PTB105511SS

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.

1. SAFETY

1.1. GENERAL SAFETY

- WARNING! Ensure Health & Safety, local authority, and general workshop practice regulations are adhered to when using these units.
 ✓ Locate the units in a suitable work area.
- Keep the work area clean, uncluttered and ensure there is adequate lighting.
- WARNING! Use the units on level and solid ground, preferably concrete.
- ✓ Keep the units clean and tidy in accordance with good workshop practice.
- ✓ Keep children and unauthorised persons away from the work area.
- **X DO NOT** use these units for any purpose other than that for which they are designed.
- **X DO NOT** use the units outdoors.
- **X DO NOT** place the units in a damp or wet location or an area where there is condensation.
- **X DO NOT** clean the units with any solvents which may damage the surfaces or the protective coating.
- X DO NOT move the units with the drawers out. To avoid tipping, open one drawer at a time and close and secure all drawers whilst moving.
- **X DO NOT** step on the drawers.

2. INTRODUCTION


- · Heavy-duty welded steel construction for strength and durability.
- . Choice of finish; textured powder coat or anti-finger-print stainless steel, both solvent and rust resistant.
- Ball bearing drawer runners (double sets on large drawers), provide superior performance and carry heavier loads.
- All drawers have full width sand blasted aluminium lift latch drawer pulls, making easy access while preventing inadvertent opening when being moved.
- Non-slip drawer liners supplied for all drawers.
- Heavy-duty Ø125mm castors on rollcabs; 2 swivel with toe brakes and 2 fixed.
- Heavy-duty exterior handles on chest and cabinets.
- · Topchests feature gas struts on lids for easy opening.
- Rollcabs (except for stainless steel versions) supplied with 12mm PVC coated MDF worktop for use as a workbench when not used with a topchest.
- Integral locking system locks all drawers in each unit with the turn of a key; all supplied with 2 keys.
- Manufactured to the highest levels of construction to withstand the toughest of workshop/garage conditions.


3. SPECIFICATION

Model No:	PTB104008SS	. PTB105511SS
Overall size (WxDxH) mm:	1055 x 460 x 565	. 1055 x 460 x 1030
Full width drawer:		. 945 x 385 x 135 (x1)
Medium drawer:	585 x 385 x 58 (x3)	. 585 x 385 x 58 (x3)
Medium 1/2 drawer:	290 x 385 x 58 (x3)	. 285 x 385 x 58 (x4)
Large drawer:	585 x 385 x 135 (x1)	. 585 x 385 x 135 (x1)
X Large drawer:		. 585 x 385 x 210 (x1)
X Large 1/2 drawer:	290 x 385 x 135 (x1)	. 285 x 385 x 210 (x1)

4. ASSEMBLY

- 4.1. These units are heavy, obtain the help of at least one other person before attempting to unpack them.
- 4.2. Install Handle (refer to fig.1).
- 4.2.1. Position the holes on the side of the rollcab and attach with the bolts provided. Tighten securely.







- 4.3. Install Casters (Rollcabs) (refer to fig.2).
- 4.3.1. Carefully lay rollcab on its back, with a soft mat underneath for protection. Position the two braked casters on the same end as the handle.
- 4.3.2. Insert the carriage bolts through washers, then through the casters and into the bottom of the cabinet. Tighten securely.
- 4.3.3. Repeat for the two free wheeling casters on the other side of the cabinet.

4.4. Remove Drawers (refer to fig.3).

- 4.1.1. Pull drawer out until it is almost fully extended. Push up one black release lever, while pulling down the other hand black release lever.
- 4.1.2. Whilst holding the levers in these positions pull the drawer out until it is released from the drawer slide.
- 4.5. **Replace Drawers**
- 4.5.1. Extend the drawer slides from the tool chest/cabinet.
- 4.5.2. Insert the brackets on each side of the drawer into the slots in the chest/cabinet slides, being careful that they are properly positioned.
- 4.5.3. Once properly inserted, completely close the drawer to set the slides in their proper positions.





4.6. Raise and Release Drawer Fronts (refer to fig.4)

- 4.6.1. These units are equipped with raise and release drawer fronts.
- 4.6.2. To open, lift up the drawer front, whilst pulling it towards you. To close, shut the drawer firmly, until the latch engages.
- 4.6.3. If the drawer does not stay closed, the hook may be bent or it may rub against the drawer slides. To fix lightly bend the hook until the drawer will engage in the slide.
- Chest and Cabinet Connection PTB104008SS PTB10511SS (refer to fig.5) 4.7.
- 4.7.1. Take out the work top from on top of the rollcab.
- 4.7.2. Place the chest on the rollcab.
- 4.7.3. Attach the connectors, as shown, to both ends.



5. MAINTENANCE

- 5.1. Lubricate the casters annually with bearing grease.
- 5.2. Lubricate the drawer slides twice a year.
- 5.3. Periodically, the drawer fronts, drawer trim and other surfaces should be cleaned with mild detergent and water.

Parts support is available for this product. To obtain a listing and/or diagram, please log on to: www.sealey.co.uk, email: sales@sealey.co.uk or phone: 01284 757500



Environmental Protection. Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycle centre and disposed of in a manner which is compatible with the environment.

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice E IMPORTANT: No liability is accepted for incorrect use of this product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Kempson Way, Suffolk Business Park, Bury St. Edmunds, Suffolk, IP32 7AR

Sole UK Distributor, Sealey Group,



Original Language Version

(PTB104008SS, PTB105511SS | Issue: 1 - 16/10/14)